

# GRAND VISTA

**GRAND VISTA with FORBID**  
is manufactured to meet the following typical properties:

Width .....	54"
Roll Size .....	30 yds.
Nominal Weight .....	36 oz. per lin. yd.
Contents .....	100% virgin vinyl
Cold Crack .....	-10°F
UV Stabilized Pigments .....	500 hrs. min.
Abrasion .....	Wyzenbeek (100,000 cycles #8 cotton duck)
Class Ratings .....	ASTM D 3690 Class A
Thickness .....	1.24 mm
Heat Sealable .....	Yes
Mildew Resistant .....	Front and Back
Anti Bacterial/Anti Microbial .....	Pass
(NYS63/ASTM G-21-90)	
Oil and Sulphide Stain Resistant .....	Yes

Suggested Applications: Conference Room, Executive Seating, Office, Residential, Hospitality, Lounge Seating, Restaurant Seating, Healthcare, Spa

Oil and Sulfide Resistant

Meets flammability requirements\*:  
Motor Vehicle Safety Standard 302  
California Technical Bulletin 117 Section E  
New York and New Jersey Port Authority  
Federal Aviation Specification 25.853  
Boston Fire Department Code  
Federal Specification CCC-A-680-A

\*\*These products have been treated with antimicrobial agents that will provide resistance to the following: (AATCC Test Method 147-1993)  
Bacillus Mycoides, Klebsiella Pneumoniae, Proteus Vulgaris, Staphylococcus Aureus, Salmonella Choleraesuis, Bacillus Cereus, Enterococcus Faecalis, Escherichia Coli

\*This term and any corresponding data refer to typical performance in the specific test indicated and should not be construed to imply the behavior of this or any other material under actual fire conditions.

FORBID dramatically increases the stain resistance, while preserving the integrity of the fabric luster and softness.

FORBID Cleaning instructions:

- Method One: For most common stains and spills, use mild soap and water.
- Method Two: If Method One doesn't work, use the following house hold items, FANTASTIK, 409, MR. CLEAN.

CLEANING METHOD	STAINING AGENT						
	Dirt	Pen Marks	Sharpie	Paint	Ketchup & Mustard	Lipstick	Nail Polish
METHOD 1	X	X					
METHOD 2	X	X			X	X	
METHOD 3		X	X	X	X	X	X

Method Three: For tougher stains such as sharpie, paint and lipstick, use a 70% isopropyl alcohol wipe.

For more information, please visit [www.forbidsrt.com](http://www.forbidsrt.com)

The Enduralex™ care guide addresses the performance of FORBID products as indicated in product testing, conducted under laboratory conditions. Results may vary under actual conditions.

The information contained in the care guide is not a guarantee and does not relieve the user of the responsibility of proper and sale use of the product and the use of recommended cleaning agents. The use of certain agents has been found to be harmful to the surface appearance and lifespan of vinyl, please familiarize yourself with those substrates for best results.

Enduralex™ topcoat, FORBID, is resistant to most common stains; however, existing dyes and pigments in some staining agents have been seen to create a permanent stain if not properly treated in a timely manner.

Enduralex™ maintains the highest vinyl production standards. Anomalies may occur during finishing if the vinyl comes into contact with incompatible forms.

